

Menu Route Map

NOTE

- Red color values indicate the default settings.
- The setting items or setting values with “*” may not be displayed depending on the availability of the optional accessories and other settings.

See the e-Manual for details on settings.

[Setup] Menu

Control Menu	
Sleep Mode	<div>High (Deep Sleep)</div> <div>Mid (Printer Sleep)</div> <div>Low (Panel Sleep)</div> <div>Off</div>
Sleep Even if Error	<div>Off</div> <div>On</div>
Sleep Migration Time	<div>5 minutes</div> <div>10 minutes</div> <div>15 minutes</div> <div>30 minutes</div> <div>60 minutes</div> <div>180 minutes</div>
Timer Settings	<div>Wake Up Timer<div>Off</div><div>On</div></div> <div>Wake Up Time<div>00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)</div></div> <div>Auto Reset Time<div>Off</div><div>10 seconds</div><div>20 seconds</div><div>30 seconds</div><div>40 seconds</div><div>50 seconds</div><div>1 minute</div><div>2 minutes</div><div>3 minutes</div><div>4 minutes</div><div>5 minutes</div><div>6 minutes</div><div>7 minutes</div><div>8 minutes</div><div>9 minutes</div></div> <div>Sleep Mode Timer<div>Off</div><div>On</div></div> <div>Sleep Mode Time<div>00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)</div></div> <div>Calibration Timer<div>Off</div><div>On</div></div> <div>Calibration Time<div>00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)</div></div>
Warning Step	<div>Toner Cart. Warning<div>Continue Printing</div><div>Stop Printing</div></div>
Auto Continue	<div>Off</div> <div>On</div>
Panel Language	<div>Čeština</div> <div>Dansk</div> <div>Deutsch</div> <div>English</div> <div>Español</div> <div>Français</div> <div>Italiano</div> <div>Magyar</div> <div>Nederlands</div> <div>Norsk</div> <div>Polski</div> <div>Português</div> <div>Русский</div> <div>Suomi</div> <div>Svenska</div>

<

Animated Instruction	<div>Off</div> <div>On</div>
Show Toner Gauge	<div>Off</div> <div>On</div>
Set. Comp. Notify	<div>Off</div> <div>1 second</div> <div>2 seconds</div> <div>3 seconds</div>
Scrolling Speed	<div>Slow</div> <div>Normal</div> <div>Fast</div>

Paper Source	<div>Paper Source<div>Auto</div><div>Drawer 1</div><div>Drawer 2*</div><div>Multi-Purpose Tray</div></div> <div>MP Tray Paper Size<div>A6</div><div>A5</div><div>A5R</div><div>B5</div><div>A4</div><div>LTR</div><div>LGL</div><div>EXEC</div><div>Mixed Sizes</div><div>Custom Size</div><div>Custom Size R</div><div>Env. ISO-C5</div><div>Env. Monarch</div><div>Env. No.10</div><div>Env. DL</div><div>Index Card</div><div>STMT</div><div>FLSC</div><div>16K</div></div> <div>MP Tray Priority<div>Off</div><div>On</div></div> <div>Drawer 1 Size<div>A6</div><div>A5</div><div>A5R</div><div>B5</div><div>A4</div><div>LTR</div><div>EXEC</div><div>Mixed Sizes</div><div>Custom Size</div><div>Custom Size R</div><div>STMT</div><div>16K</div></div> <div>Drawer 2 Size*<div>Mixed Sizes</div><div>Auto</div><div>Custom Size</div><div>Custom Size R</div><div>FLSC</div><div>16K</div></div> <div>Standard Paper Size<div>A6</div><div>A5</div><div>B5</div><div>A4</div><div>LTR</div><div>LGL</div><div>EXEC</div><div>Env. ISO-C5</div><div>Env. Monarch</div></div>
--------------	---

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

Diff. Paper Tray

Off

On

Auto Selection

Multi-Purpose Tray

Off

On

Drawer 1

Off

On

Drawer 2*

Off

On

Default Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Transparency

Envelope

Labels

Rough

MP Tray Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Transparency

Envelope

Labels

Rough

Mixed Types

Drawer 1 Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Rough

Mixed Types

Drawer 2 Type*

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Rough

Mixed Types

Manual 2-Sided (MP)

1st Side

2nd Side

2-Sided Printing

Off

On

Network

TCP/IP Settings

IPv4 Settings

IPv4: Off, On

IP Mode: Auto, Manual

Protocol*

Use DHCP: Off, On

Use BOOTP: Off, On

Use RARP: Off, On

IP Address Settings

IP Address: 0.0.0.0

Subnet Mask: 0.0.0.0

Gateway Address: 0.0.0.0

DNS

Primary Address: 0.0.0.0

Secondary Address: 0.0.0.0

DHCP Option

Acquire Host Name: Off, On

DNS Dynamic Update: Off, On

IPv6 Settings

IPv6: Off, On

WINS Resolution

Off

On

ARP/PING

Off

On

FTP

FTP Print: Off, On

FTP Settings: Off, On

LPD Print

Off

On

RAW Print

Off

On

IPP Print

Off

On

WSD

WSD Print: Off, On

WSD Browsing*: Off, On

Multicast Discovery: Off, On

HTTP

Off

On

Proxy Settings*

Proxy: Off, On

Server Address*

Port Number*: 0 to 80 to 99999

Same Domain*: Use Proxy, Do Not Use Proxy

Proxy Authentication*: Off, On

User Name*

Password*

SNTP

Off

On

Discovery Response

Off

On

IPSec

Off

On

NetWare Settings

NetWare

Off

On

Frame Type*

Auto Detect

Ethernet II

Ethernet 802.2

Ethernet 802.3

Ethernet SNAP

Print Service*

Bindery PServer

RPrinter

NDS PServer

NPrinter

AppleTalk

Off

On

SMB*

SMB Server

Off

On

SMB Print

Off

On

SNMP Settings

SNMP v. 1 Settings

SNMP v. 1: Off, On

Dctd. Community Set.

Dctd. Community: Off, Read/Write, Read Only

SNMP v. 3 Settings

SNMP v. 3: Off, On

User Settings 1 to User Settings 5*: Auth. Password, Encryption Password

Rjct Packet in Sleep

Off

On

Spooler*

Off

On

Network Delay Time

0 to 300 seconds

Remote UI Settings

Remote UI: Off, On

SSL*: Off, On*

Ethernet Driver

Auto Detect

Off

On

Communication Mode*

Half Duplex

Full Duplex

Ethernet Type*

10 Base-T

100 Base-TX

1000 Base-T

IEEE802.1X

Off

On

Address Filter

Off

On

MAC Address

(Display only)

E-Mail Print Set.

POP3 RX Interval

0 to 90 (minutes)

POP3 RX

Off

On

SMTP RX

Off

On

Init. Network Set.

Layout

Copies

1 to 9999

Offset Y/Offset X

-1.97 to 0.00 to +1.97 (in.)

Binding Location

Long Edge

Short Edge

Gutter

-1.97 to 0.00 to +1.97 (in.)

Alternative Method

Off

On

Quality

Gradation Level

High 1

High 2

Toner Save

Off

On

Density: C*

-8 Light to 0 to +8 Dark

Density: M*

-8 Light to 0 to +8 Dark

Density: Y*

-8 Light to 0 to +8 Dark

Density: K*

-8 Light to 0 to +8 Dark

Density C (Fine Adj)*

High

-8 Light to 0 to +8 Dark

Mid

-8 Light to 0 to +8 Dark

Low

-8 Light to 0 to +8 Dark

Density M (Fine Adj)*

High

-8 Light to 0 to +8 Dark

Mid

-8 Light to 0 to +8 Dark

	Low <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
Density Y (Fine Adj)*	High <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
	Mid <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
	Low <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
Density K (Fine Adj)*	High <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
	Mid <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
	Low <ul style="list-style-type: none">-8 Light to 0 to +8 Dark
Color Mode	Auto (Color/Black)
	Color
	Black
Halftones	Error Diffusion <ul style="list-style-type: none">OffOn
	Resolution/Grad. <ul style="list-style-type: none">Text: Resolution, GradationGraphics: Resolution, GradationImage: Resolution, Gradation
Gray Compensation	Text <ul style="list-style-type: none">OffOn
	Graphics <ul style="list-style-type: none">OffOn
	Image <ul style="list-style-type: none">OffOn
CMS	CMS Selection <ul style="list-style-type: none">PrinterHost
	CMS/Gamma <ul style="list-style-type: none">Text: CMS, GammaGraphics: CMS, GammaImage: CMS, Gamma
	RGB Source Profile <ul style="list-style-type: none">Text: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4Graphics: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4Image: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
	Output Profile <ul style="list-style-type: none">Text: Normal, PhotoGraphics: Normal, PhotoImage: Normal, Photo
	Matching Method <ul style="list-style-type: none">Text: Perceptual, Saturation, ColorimetricGraphics: Perceptual, Saturation, ColorimetricImage: Perceptual, Saturation, Colorimetric
	Gamma Correction <ul style="list-style-type: none">Text: 1.0, 1.4, 1.8, 2.2Graphics: 1.0, 1.4, 1.8, 2.2Image: 1.0, 1.4, 1.8, 2.2
Gradation Settings	Gradation <ul style="list-style-type: none">OffSmooth 1Smooth 2
	Graphics <ul style="list-style-type: none">OffOn
	Image <ul style="list-style-type: none">OffOn
Advanced Smoothing	Advanced Smoothing <ul style="list-style-type: none">OffSmooth 1Smooth 2

	Graphics <ul style="list-style-type: none">OffOn
	Text <ul style="list-style-type: none">OffOn
Toner Volume Corr.	Normal
	Gradation Priority
	Text Priority
Line Control	Resolution Priority
	Gradation Priority
Reduce Quality	Continue Printing
	Stop Printing

Interface	Interface Selection* <ul style="list-style-type: none">USB<ul style="list-style-type: none">OffOnNetwork<ul style="list-style-type: none">OffOnUSB Storage Device, MEAP Driver<ul style="list-style-type: none">OffOn
Timeout	Timeout <ul style="list-style-type: none">OffOn
	Timeout Time* <ul style="list-style-type: none">5 to 15 to 300 seconds
Connection Recog.*	Off
	On
Extended RX Buffer*	Off
	On

User Maintenance	Adj. Start Position <ul style="list-style-type: none">Offset Y (MP Tray)<ul style="list-style-type: none">-0.20 to 0.00 to +0.20 (in.)Offset X (MP Tray)<ul style="list-style-type: none">-0.09 to 0.00 to +0.09 (in.)Offset Y (Drawer 1)<ul style="list-style-type: none">-0.20 to 0.00 to +0.20 (in.)Offset X (Drawer 1)<ul style="list-style-type: none">-0.09 to 0.00 to +0.09 (in.)Offset Y (Drawer 2)*<ul style="list-style-type: none">-0.20 to 0.00 to +0.20 (in.)Offset X (Drawer 2)*<ul style="list-style-type: none">-0.09 to 0.00 to +0.09 (in.)Offset Y (2-Sided)<ul style="list-style-type: none">-0.20 to 0.00 to +0.20 (in.)Offset X (2-Sided)<ul style="list-style-type: none">-0.09 to 0.00 to +0.09 (in.)
Recovery Printing	Off
	On
Check Paper Size	Off
	On
Substitute Size	Off
	On
Special Image Mode	Off
	Level 1
	Level 2
SD Card Maintenance	Format <ul style="list-style-type: none">NoYes
Special Print Mode	Curl Correction <ul style="list-style-type: none">OffOn

Smooth Plain Paper	Off
	On
Update Firmware	USB
	Network
First Calibration	Off
	After Jobs
	Immediately
Paper Feed Method	Multi-Purpose Tray <ul style="list-style-type: none">Speed PriorityPrint Side Priority
	Drawer 1 <ul style="list-style-type: none">Speed PriorityPrint Side Priority
	Drawer 2* <ul style="list-style-type: none">Speed PriorityPrint Side Priority
Adjust Standby Temp	Off
	Mode 1
	Mode 2
	Mode 3
Show Job List	Off
	On
IMPORT/EXPORT	EXPORT
	IMPORT

Print Mode	Auto Mode Selection <ul style="list-style-type: none">Auto SelectionPCLPSPDFXPS
	Auto Select <ul style="list-style-type: none">PCL<ul style="list-style-type: none">OffOnPS<ul style="list-style-type: none">OffOnPDF<ul style="list-style-type: none">OffOnXPS<ul style="list-style-type: none">OffOn
	Mode Priority <ul style="list-style-type: none">NonePCLPSPDFXPS

UFR II	Paper Save <ul style="list-style-type: none">OffOn
--------	--

PCL	Paper Save <ul style="list-style-type: none">OffOn
	Orientation <ul style="list-style-type: none">PortraitLandscape
	Font Number <ul style="list-style-type: none">0 to 104
	Point Size* <ul style="list-style-type: none">4.00 to 12.00 to 999.75 point
	Pitch* <ul style="list-style-type: none">0.44 to 10.00 to 99.99 cpi
	Form Lines <ul style="list-style-type: none">5 to 60 to 128 lines

Character Code

PC8

ROMAN8

ROMAN9

ISOL1

ISOL2

ISOL5

ISOL6

ISOL9

PC775

PC8DN

PC850

PC852

PC858

PC8TK

PC1004

WINL1

WINL2

WINL5

WINBALT

DESKTOP

PSTEXT

LEGAL

ISO4

ISO6

ISO11

ISO15

ISO17

ISO21

ISO60

ISO69

WIN 30

MCTEXT

PC864

ARABIC8

WINARB

PC866

ISOCYR

WINCYR

PC851

GREEK8

ISOGRK

PC8GRK

WINGRK

PC862

HEBREW7

HEBREW8

ISOHEB

Custom Size

Do Not Set

Set

Unit of Measurement*

Millimeters

Inches

X Dimension*

3.00 to 8.50 in. (76.2 to 215.9 mm)

Y Dimension*

5.00 to 14.00 in. (127.0 to 355.6 mm)

Append CR to LF

Yes

No

Enlarge A4 Prt Width

Off

On

BarDIMM*

Enable

Disable

FreeScape*

Off

~

"

#

\$

/

\

?

{

}

|

Imaging

Image Orientation

Auto

Vertical

Horizontal

Zoom

Off

Auto

Print Position

Auto

Center

Top Left

Print Guarantee*

Off

On

Show Warnings

Off

Print

Panel

Print E-Mail Text

On

Off

Limit E-Mail Print*

Off

On

Enlarge Print Area

Off

On

RGB Source Profile

sRGB v3.0 (Canon)

Canon HDTV gamma 1.5

Canon HDTV gamma 1.8

Canon HDTV gamma 2.4

CMYK Sim. Profile

Euro Standard v1.00

JapanColor (Canon)

U.S. Web Coated v1.0

Output Profile

Normal

Photo

Matching Method

Perceptual

Saturation

Colorimetric

Halftones

Resolution

Gradation

Error Diffusion

Photo Corr (CL Only)*

Photo Optimizer PRO

Off

On

Red-Eye Correction

Red-Eye Correction: Off, On

Red-Eye Correct. Lv.*: Weak, Standard, Strong

Face Brightener

Face Brightener: Off, On

Face Brightener Lv.*: Weak, Standard, Strong

Grayscale Conversion*

sRGB

NTSC

Uniform RGB

XPS

Matching Mode

ICC Profile

Gamma

ICC Profile Settings

RGB Source Profile

Text: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4

Graphics: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4

Image: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4

Output Profile

Text: Normal, Photo

Graphics: Normal, Photo

Image: Normal, Photo

Matching Method

Text: Perceptual, Saturation, Colorimetric

Graphic: Perceptual, Saturation, Colorimetric

Image: Perceptual, Saturation, Colorimetric

Gamma Settings

Gamma Correction

Text: 1.0, 1.4, 1.8, 2.2

Graphics: 1.0, 1.4, 1.8, 2.2

Image: 1.0, 1.4, 1.8, 2.2

Photo Corr (CL Only)

Photo Optimizer PRO

Off

On

Red-Eye Correction

Red-Eye Correction: Off, On

Red-Eye Correct. Lv.*: Weak, Standard, Strong

Face Brightener

Face Brightener: Off, On

Face Brightener Lv.*: Weak, Standard, Strong

Halftones

Error Diffusion: Off, On

Resolution/Grad.*

Text: Resolution, Gradation

Graphics: Resolution, Gradation

Image: Resolution, Gradation

Gray Compensation

Text

Off

On

Graphics

Off

On

Image

Off

On

Advanced Smoothing

Advanced Smoothing

Off

Smooth 1

Smooth 2

Graphics*

Off

On

Text*

Off

On

Grayscale Conversion

Text

sRGB

NTSC

Uniform RGB

Graphics

sRGB

NTSC

Uniform RGB

Image

sRGB

NTSC

Uniform RGB

PDF

Fit to Page

Off

On

Enlarged Print Area

Off

On

N on 1

Off

2 on 1

4 on 1

6 on 1

8 on 1

9 on 1

16 on 1

Comment Print

Off

Auto

4

ICC Profile Settings

RGB Source Profile

sRGB v3.0 (Canon)

Canon HDTV gamma 1.5

Canon HDTV gamma 1.8

Canon HDTV gamma 2.4

None

CMYK Sim. Profile

Euro Standard v1.00

JapanColor (Canon)

U.S. Web Coated v1.0

None

Grayscale Profile

Off

On

Output Profile

PS Normal

PS Photo

PS TR Normal

PS TR Photo

Matching Method

Perceptual

Saturation

Colorimetric

RGB Pure Black Mode

Off

On

CMYK Pure Black

Off

On

Pure Black Text

Off

On

Black Overprint*

Off

On

Brightness

85 to 100 to 115%

Halftones

Error Diffusion

Off

On

Resolution/Grad.

Text: Resolution, Gradation

Graphics: Resolution, Gradation

Image: Resolution, Gradation

CMYK Overprint

Off

On

Advanced Smoothing

Advanced Smoothing

Off

Smooth 1

Smooth 2

Graphics*

Off

On

Text*

Off

On

Grayscale Conversion*

sRGB

NTSC

Uniform RGB

PS

Job Timeout

0 to 3600 seconds

Print PS Errors

Off

On

ICC Profile Settings

RGB Source Profile

sRGB v3.0 (Canon)

Canon HDTV gamma 1.5

Canon HDTV gamma 1.8

Canon HDTV gamma 2.4

None

CMYK Sim. Profile

Euro Standard v1.00

JapanColor (Canon)

U.S. Web Coated v1.0

None

Grayscale Profile

Off

On

Output Profile

PS Normal

PS Photo

PS TR Normal

PS TR Photo

Matching Method

Perceptual

Saturation

Colorimetric

RGB Pure Black Mode

Off

On

CMYK Pure Black

Off

On

Pure Black Text

Off

On

Black Overprint*

Off

On

Brightness*

85 to 100 to 115%

Halftones

Error Diffusion

Off

On

Resolution/Grad.

Text: Resolution, Gradation

Graphics: Resolution, Gradation

Image: Resolution, Gradation

CMYK Overprint

Off

On

Advanced Smoothing

Advanced Smoothing

Off

Smooth 1

Smooth 2

Graphics*

Off

On

Text*

Off

On

Grayscale Conversion*

sRGB

NTSC

Uniform RGB

MEAP Settings

Select Def. Screen

Print Screen

MEAP

Check Counter

101: Total 1*

(Display only)

102: Total 2*

(Display only)

108: Total (Black 1)*

(Display only)

109: Total (Black 2)*

(Display only)

322: Print(Full+1C/S)*

(Display only)

[Utility Menu] Menu

Check Counter

101: Total 1*

(Display only)

102: Total 2*

(Display only)

108: Total (Black 1)*

(Display only)

109: Total (Black 2)*

(Display only)

322: Print(Full+1C/S)*

(Display only)

Configuration Page

Network Status Print

IPSec Policy List

Calibration

Color Mismatch Corr.

Density Control

Density Median Cont.

Full Calibration

PCL Utility

Font List

PS Utility

Configuration Page

Font List

Cleaning

A4

LTR

E-Mail Print Utility

Received E-Mails

Received E-mail List

Printing Pos. Print

Page Count List

Counter Report

Print MEAP Sys. Info

Serial Number

(Display only)

Consumables

Paper Information

Toner Cart. Model

Remaining Toner

[Job] Menu

Encrypted Print*

User Name

Job Name

PIN

Secured Print*

User Name

Job Name

PIN

Stored Job List*

Stored Job Print*

Box No.N (N=0 to 99)

PIN

Job Name

Job Print Log List*

Stored Job Print Log*

Report Print Log*

E-Mail Print Log*

[Reset] Menu

Soft Reset (Hard Reset)

Form Feed

Shut Down

[Select Feeder] Menu

Paper Source

Auto

Drawer 1

Drawer 2*

Multi-Purpose Tray

MP Tray Paper Size

A6

A5

A5R

B5

A4

LTR

LGL

EXEC

Mixed Sizes

Custom Size

Custom Size R

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

MP Tray Priority

Off

On

Drawer 1 Size

A6

A5

A5R

B5

A4

LTR

EXEC

Mixed Sizes

Custom Size

Custom Size R

STMT

16K

Drawer 2 Size*

Mixed Sizes

Auto

Custom Size

Custom Size R

FLSC

16K

Standard Paper Size

A6

A5

B5

A4

LTR

LGL

EXEC

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

Diff. Paper Tray

Off

On

Auto Selection

Multi-Purpose Tray

Off

On

Drawer 1

Off

On

Drawer 2*

Off

On

Default Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Transparency

Envelope

Labels

Rough

MP Tray Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Transparency

Envelope

Labels

Rough

Mixed Types

Drawer 1 Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Rough

Mixed Types

Drawer 2 Type*

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Rough

Mixed Types

Manual 2-Sided (MP)

1st Side

2nd Side

2-Sided Printing

Off

On